Engineering Specification

Contractor
Approval
Contractor's P.O. No.
Representative

LEAD FREE*

Series LF709

Double Check Valve Assemblies

21/2" - 10"

Series LF709 Double Check Valve assemblies help prevent the reverse flow of polluted water from entering into the potable water system. This series can be applied, where approved by the local authority having jurisdiction, on non-health hazard installations. The series features a modular check design concept to facilitate maintenance. Check with local jurisdictional authority as to installation requirements. The valve body is fused with ArmorTekTM technology to resist corrosion due to microbial induced corrosion (MIC) or exposed metal substrate. The series also features Lead Free* construction to comply with Lead Free* installation requirements.

Features

- Simplified modular design concept to facilitate complete maintenance and assembly by retaining the spring load
- Replaceable stainless steel seats
- Maximum flow at low pressure drop
- Advanced ArmorTek[™] coating technology to resist corrosion of internals
- No special tools required for servicing
- · Captured spring assemblies for safety
- Approved for vertical flow up installation

Specification

A Double Check Valve Assembly shall be installed at referenced crossconnections to prevent the backflow of polluted water into the potable water supply. The cross-connections shall be determined by local inspection authority for use where a high hazard situation does not exist. Valve shall feature modular check assemblies with center stem guiding. Each check module shall have a captured spring and be accessible through a bolted cover plate. Seats shall be replaceable without special tools. It shall be a complete assembly including tight-closing resilient seated shutoff valves, test cocks, and a strainer is recommended. The Lead Free* Double Check Assemblies shall comply with state codes and standards, where applicable, requiring reduced lead content. The assembly shall meet the requirements of ASSE No. 1015; AWWA C510-92; CSA B64.5 and UL Classified File No. EX3185. Approved by the Foundation for Cross-Connection Control and Hydraulic Research at the University of Southern California. The valve body shall utilize a coating system with built in electrochemical corrosion inhibitor and microbial inhibitor. Assembly shall be a Watts Series LF709.



NOTICE

For IOT models, an add-on monitoring connection kit is required to collect psi measurements from the integrated pressure sensors. Without the connection kit, the pressure sensors are passive components and will not communicate with any other device. For BMS only. (The connection kit and pressure sensors are also available for existing installations. For more information, download RP/IS-709/709DCDA.)

NOTICE

Use of integrated pressure sensors on and monitoring connection kit with IOT models does not remove the need to comply with all required instructions, codes, and regulations related to installation, operation, and maintenance of the backflow preventer.

Watts® is not responsible for data transmission failures due to power issues.

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Inquire with governing authorities for local installation requirements.



^{*}The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Model/Option

NRS Non-rising stem resilient seated gate valves

OSY UL Classified and FM Approved outside stem and yoke

resilient seated gate valves

S-FDA FDA epoxy coated strainer LF Without shutoff valves

IOT With pressure sensing IoT test cocks and NRS gate valves

QT-FDA FDA epoxy coated quarter-turn ball valve shutoffs

Materials

Check Valve Body: Epoxy coated cast iron

Seats: Stainless steel
Coating technology: Armortek


Pressure - Temperature

Temperatures Range: 33°F - 110°F (0.5°C - 43°C) continuous,

140°F (60°C) intermittent

Maximum Working Pressure: 175 psi (12.1 bar)

Dimensions — Weights



	21111121212															
SIZE	DIMENSIONS															
	Α		C (0	OSY)	C (N	IRS)	D		L		U†		M		N	
in.	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm
21/2	397/16	1002	16%	416	93%	238	31/2	89	24 ¹ / ₈	613	11	279	10	254	6½	165
3	407/16	1027	187//8	479	101/4	260	3¾	95	24 ¹ / ₈	613	14	356	10 ¹ / ₈	257	7	178
4	52%	1332	22¾	578	123/16	310	4½	114	341/8	867	14	356	12 ¹ /8	308	81/4	210
6	6215/16	1599	301//8	765	16	406	5½	140	41 ⁵ /8	1058	16	406	18½	470	13½	343
8	75 ⁷ ⁄ ₁₆	1916	37¾	959	19 ¹⁵ / ₁₆	506	6½	165	52 ¹ / ₈	1325	21	533	21 ⁵ /8	549	15½	394
10	907/16	2297	45¾	1162	2313/16	605	8	203	641/8	1630	25	635	26	660	181/2	470

SIZE	DIMENSIONS									WEIGHT						
	N1††		N1†† R		R*		Т		NRS		OSY		QT		Weight	
in.	in.	mm	in.	mm	in.	mm	in.	mm	lb	kg	lb	kg	lb	kg	lb	kg
21/2	10	254	4	102	16	406	3	76	167	76	170	77	154	70	28	13
3	10	254	5	127	16	406	3	76	167	76	170	77	162	73	34	15
4	12	305	6	152	19¾	502	6	152	368	167	383	174	275	125	60	27
6	20	508	11	279	26	660	7½	191	627	284	707	321	611	277	122	55
8	22¾	578	111/4	286	111/4	286	9	229	1201	545	1307	593	1419	644	247	112
10	28	711	12½	318	12½	318	101/4	260	2003	909	2073	940	2466	1119	370	168

†Service clearance for check assembly from center.

††Dimension required for screen removal.

*Quarter-turn (QT) valve dimensions.

Standards

AWWA C510-92 IAPMO PA 31

USC Manual for Cross-Connection Control, 8th Edition

Approvals












Approved by the Foundation for Cross-Connection Control and Hydraulic Research at the University of Southern California. Sizes 4" to 10" approved horizontal and vertical "flow up." Sizes 2½" and 3" approved horizontal only.

FM Approved 4" to 10" vertical "flow up" with OSY gate valves only.


Note: Model "S" not listed.



Capacity

‡Typical maximum system flow rate (7.5 ft/sec) **UL rated flow







USA: T: (978) 689-6066 • Watts.com Canada: T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-LF709 2304 © 2023 Watts